


# QRC-FLEX 4K

## Gold Mount Power Solution for the Phantom FLEX4K

The QRC-FLEX 4K Gold Mount® installs quickly on the Vision Research Phantom FLEX4k camera for use with Anton/Bauer DIGITAL and Logic Series® batteries. A single PowerTap® output is provided to power accessories.



Vision Research  
Phantom Flex4K



QRC-FLEX 4K



CINE VCLX

CINE VCLX/2

### CINE series

Simultaneous 14.4V and 28V outputs,  
providing extended run-times



DIGITAL Battery  
Series



DIONIC®  
Series



HyTRON®  
Series

### APPROXIMATE RUN-TIMES (based on 150w load)

DIGITAL Series		DIONIC Series		HyTRON Series		CINE-VCLX Series	
DIGITAL 90	1/2 hr	DIONIC HC	1/2 hr			CINE-VCLX	3-3/4 hrs
DIGITAL 150	1 hr	DIONIC HCX	3/4 hr	HyTRON 140	3/4 hr	CINE-VCLX/2	1-3/4 hrs
DIGITAL 190	1-1/2 hrs	DIONIC HD	1-1/2 hrs				

Americas  
Vitec Videocom Inc  
14 Progress Drive  
Shelton  
CT 06484  
United States  
T +203-929-1100  
F +203-925-2684  
E salesupport\_USA@vitecgroup.com

EMEA & Asia  
Vitec Videocom GmbH  
Erfurter Str. 16  
85386 Eching  
Germany  
T +49 (0) 89 32158-200  
F +49 (0) 89 32158-227  
E salesupport\_EMEA@vitecgroup.com  
E salesupport\_ASIA@vitecgroup.com

Japan  
Vitec Videocom KK  
Shibakoen 3-chome Bldg. 1F  
3-1-38 Shibakoen Minato-ku  
Tokyo 105-0011  
Japan  
T +81 (0)3 5777 8040  
F +81 (0)3 5777 8041  
E salesupport\_Japan@vitecgroup.com